



SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
VH-2A2	3.96	7.92
VH-3A3 (VH-3A2)	7.92	11.88
VH-4A4	11.88	15.84
VH-5A5	15.84	19.80
VH-6A6	19.80	23.76
VH-7A7	23.76	27.72
VH-8A8	27.72	31.68
VH-9A9	31.68	35.64
	35.64	39.60
	39.60	43.56
	43.56	47.52

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	钱岳生 2013、07、01	料号 PART NO.	版本 REV.
			X.±0.25	X.'±2'	审核 CHECK	张名 2013、07、03	VH直针 WAFER DIP TYPE	A
			.X±0.20	.X'±1'	核准 APPROVAL	张名 2013、07、05	客户料号 CUTL. NO.	页次 SHEET
			.XX±0.15	.XX'±0.5'	单位 UNITS	MM	比例 SCALE	1:1
			.XXX±0.10	.XXX'±0.5'	深圳市华灿电子有限公司			

