



SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25°C~+85°C
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated



PCB LAYOUT

编 号	尺寸 (mm)	
	A	B
VH-2A2W	3.96	7.92
VH-3A3W (VH-3A2W)	7.92	11.88
VH-4A4W	11.88	15.84
VH-5A5W	15.84	19.80
VH-6A6W	19.80	23.76
VH-7A7W	23.76	27.72
VH-8A8W	27.72	31.68
VH-9A9W	31.68	35.64
VH-10A10W	35.64	39.60
	39.60	43.56
	43.56	47.52

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENREL TOLERANCE		制图 DRAWING	钱岳生		料号 PART NO.	VH-NANW		版本 REV.	A				
			X.±0.25	X.*±2'		审核 CHECK	2013、07、01		品名 TITLE	VH平弯		页次 SHEET	1/1			
			.X±0.20	.X*±1'			核准 APPROVAL			2013、07、03			客户料号 CUTM. NO.	WAFER DIP TYPE		
			.XX±0.15	.XX*±0.5'						张名						
.XXX±0.10	.XXX*±0.5'	单位 UNITS	MM	比例 SCALE	1:1		深圳市华灿天禄电子有限公司									