



2~5A

SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~+85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66, UL94V-0
PIN Brass Tin-plated

编 号	尺寸 (mm)	
	A	B
XA-2A	2.50	7.50
XA-3A	5.00	10.00
XA-4A	7.50	12.50
XA-5A	10.00	15.00
XA-6A	12.50	17.50
XA-7A	15.00	20.00
XA-8A	17.50	22.50
XA-9A	20.00	25.00
XA-10A	22.50	27.50
XA-11A	25.00	30.00
XA-12A	27.50	32.50

PCB LAYOUT

GENERAL TOLERANCE		制 图 DRAWING 2015、07、01	线 岳 生 2015、07、01	料 号 PART NO. XA-NA	版 本 REV. A							
X.±0.25	X.'±2'					审 核 CHECK 2015、07、03	张 名	品 名 TITLE WAFER DIP TYPE	页 次 SHEET 1/1			
.X±0.20	.X'±1'									核 准 APPROVAL 2015、07、03	张 名	客 户 料 号 CUTL NO.
.XX±0.15	.XX'±0.5'											
.XXX±0.10	.XXX'±0.5'	富 港 电 子										