

GT-TC126X-HXXX-LX

G-SWITCH

Operating Force



- A=160gf
- B=250gf
- D=350gf
- F=320gf
- G=400gf
- H=600gf

Switch Height (mm)


- H031=3.1mm
- H034=3.4mm
- H035=3.5mm
- H043=4.3mm
- H050=5.0mm
- H052=5.2mm

Switch lifetime (Force)

- L1=100,000 Cycles(D)
- L3=300,000 Cycles(A, B)
- L5=500,000 Cycles(A, B)



P.C.B LAND DIMENSION



CIRCUIT DIAGRAM



RoHS
Compliant
2002/95/EC



Compliant
Halogen Free



G-Switch Electronic (HongKong) CO.,Ltd.

Unless otherwise specified, Tolerance:
 X. ±0.30
 X.x ±0.20
 X.xx ±0.15
 X.xxx ±0.10
 Angles ±3°

DESIGN FengFengChen DATE 2019.05.29
 CHECKED DATE
 APPROVED DATE
<http://www.dg-switch.com>
 TEL:0769-82388879

Molde code:
 GT-TC126X-HXXX-LX
 REV.: X1 SCALE: 4:1 UNIT: mm
 SIZE: A4 SHEET: 1/1