


料号 material No.	品名 Parts Name	型号 Part NO.	螺钉口直径 screw dia.	美制螺栓号 USA screw
40-SVS1.25-3.5	叉形预绝缘端子	SVS1.25-3.5	3.7	#6



导线截面: 0.5-1.5mm<sup>2</sup> (美国线规22-16)  
 最大电流: I<sub>max</sub>=19A  
 材 质: 紫铜 PA66  
 颜色: 红色/黑色  
 材料厚度: 0.75mm  
 Cable size: 0.5~1.5mm(A.W.G.22~16)  
 Max current : I<sub>max</sub>=19A  
 Material: purple copper PA66  
 Color: red/black.  
 Thickness: 0.75mm



未经许可不得修改和复印  
 该知识产权属于技术质量部

DIMENSION		TOLERANCES		FIRST ANGLE PROJ		L.T.R.		NEW PART		DWC. BY		CHK. BY		DATE	
0.0	0.00	±1.0		A											
DWG. BY		CHK. BY		APP. BY		L.T.R.		REVISION RECORD		DWC. BY		CHK. BY		DATE	
Liu Liang		Callian		wang zhiyan		A				Callian		zy_wang		202105	
UNIT		REV.		DWG. NO.											
mm		A		HIMA/QR-JZ-40-SVS1.25-3.5											

HIMA 惠华 苏州惠华电子科技有限公司