



P/N LEGEND

A1250		WV	-XP	N	X	X	XX	N	00	B
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩	

① Series No.  
 ② Connector type: WV=Vertical  
 ③ No. of circuits  
 ④ N=Halogen Free  
 ⑤ Material: L=LCP-V0 ; 6=Nylon 6T  
 ⑥ Color: B=Black N=Natural  
 ⑦ Plating code for contacts: T1=Tin-plated  
 S4=Gold-plated 10u"on contact area,  
 Gold-flash on solder area  
 ⑧ Plating code: N=Non-plating  
 ⑨ Option code: 00=Standard  
 ⑩ Packing code: B=Tray

SPECIFICATIONS

Current Rating: 1A AC,DC  
 Voltage Rating: 125V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 20mΩ Max.  
 Insulation Resistance: 100MΩ Min.  
 Withstanding Voltage: 500V AC/minute  
 Pin Material: Phosphor Bronze/Tin-plated

Ordering Information & Dimensions

Circuit No.	Dimensions		Circuit No.	Dimensions	
	A	B		A	B
02P	1.25	4.25	11P	12.50	15.50
03P	2.50	5.50	12P	13.75	16.75
04P	3.75	6.75	13P	15.00	18.00
05P	5.00	8.00	14P	16.25	19.25
06P	6.25	9.25	15P	17.50	20.50
07P	7.50	10.50	16P	18.75	21.75
08P	8.75	11.75	17P	20.00	23.00
09P	10.00	13.00	18P	21.25	24.25
10P	11.25	14.25			

燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.				UNIT	SCALE	SHEET	TITLE:
				mm	1 : 1	1 of 1	
DRAWN BY 周傑亮 2013. 11. 15				APPROVED BY 張子波 2013. 11. 15		1.25mm PITCH 180° WAFER	
A2	EN141110001	2014. 11. 10	劉建芳	X. X±0. 25	DRAW NO. : A1250WV-XPXXXXXXX		REV. A2
A1	EN1408220004	2014. 08. 22	黃培軍	X. XX±0. 15			
A0	NEW RELEASE	2013. 11. 15	周傑亮	X. XXX±0. 05			
REV.	DESCRIPTION	DATE	NAME				