

P/N LEGEND

A1501	WV-S-XP	N	X	X	XX	N	00	L
①	②	③	④	⑤	⑥	⑦	⑧	⑨

① Series No.
 ② Connector type: WV=Vertical
 ③ S=SMT
 ④ No. of circuits
 ⑤ N=Halogen Free
 ⑥ Material: 6=Nylon 6T,UL94V-0 ; L=LCP,UL94V-0
 ⑦ Color: N=Natural ; B=Black
 ⑧ Plating code for contacts:
 T1=Tin-plated ; G1=Gold-Flash
 ⑨ Plating code: N=Non-plating
 ⑩ Option code: 00=Standard
 ⑪ Packing code: L=Tape Reel(With Cap or Mylar)

SPECIFICATIONS

Current Rating: 3A AC,DC
 Voltage Rating: 350V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 20mΩ Max.
 Insulation Resistance: 1000MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Pin Material: Brass


Ordering Information & Dimensions

PART NO.	Dimensions	
	A	B
02P	1.50	4.30
03P	3.00	5.80
04P	4.50	7.30
05P	6.00	8.80
06P	7.50	10.30
07P	9.00	11.80
08P	10.50	13.30
09P	12.00	14.80
10P	13.50	16.30
11P	15.00	17.80
12P	16.50	19.30
13P	18.00	20.80
14P	19.50	22.30
15P	21.00	23.80



				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.	
UNIT		SCALE	SHEET		TITLE:
mm		1 : 1	1 of 2		
DRAWN BY		APPROVED BY		1.50mm PITCH 180° WAFER-SMT TYPE	
郭木思		陳彥兆			
2016.02.25		2016.02.25		DRAW NO. : A1501WV-S-XPXXXXXXXXXX	
GENERAL TOLERANCE					
X. X±0.25		ANGLE±		REV. AO	
X. XX±0.15					
X. XXX±0.05					
A0	NEW RELEASE	2016.02.25	郭木思		
REV.	DESCRIPTION	DATE	NAME		



02~09 Contacts




Unreeling direction →







Number of Contacts	W±0.3	F±0.1	S±0.1	Q'ty/Reel
02P	16	7.50	/	500
03P	16	7.50		500
04P	16	7.50		500
05P	24	11.50		500
06P	24	11.50		500
07P	24	11.50		500
08P	24	11.50		500
09P	24	11.50		500
10P	32	14.20		28.40
11P	32	14.20	28.40	500
12P	32	14.20	28.40	500
13P	32	14.20	28.40	500
14P	44	20.20	40.40	500
15P	44	20.20	40.40	500

10~15 Contacts



Unreeling direction →



				JOINT TECH ELECTRONIC IND. CO., LTD.		JOY DAY INDUSTRIAL CO., LTD.	
				UNIT	SCALE	SHEET	TITLE:
				mm	1 : 1	2 of 2	1.50mm PITCH 180° WAFER-SMT TYPE TAPING SPEC.
				DRAWN BY	APPROVED BY		
				郭本恩	陳彥兆		
				2016.02.25	2016.02.25		
				GENERAL TOLERANCE			
				X. X±0.25	ANGLE±		DRAW NO. : A1501WV-S-XPXXXXXXX
				X. XX±0.15			
A0	NEW RELEASE	2016.02.25	郭本恩	X. XXX±0.05			REV.
REV.	DESCRIPTION	DATE	NAME				A0