



Ordering code

A2006 WV-XP XXX			
①	②	③	④
① Series No.			
② Connector type: WV=Vertical			
③ No. of circuits			
④ Option code:			
Blank=Color/Beige; Dim. E=3.20mm			
BK =Color/Black; Dim. E=3.20mm			
Y01 =Color/Beige; Dim. E=2.10mm			

SPECIFICATIONS

Current Rating: 3A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 30mΩ Max.
 Insulation Resistance: 1000MΩ Min.
 Withstanding Voltage: 1000V AC/minute
 Pin Material: Brass/Gold-flash
 Material: Nylon 46,UL94V-0
 Color: Beige or Black

Circuit No.	Dimensions			
	A	B	C	D
02P	2.00	6.00	1.50	4.90
03P	4.00	8.00	1.46	6.90
04P	6.00	10.00	3.46	8.90
05P	8.00	12.00	5.46	10.90
06P	10.00	14.00	7.46	12.90
07P	12.00	16.00	9.46	14.90
08P	14.00	18.00	11.46	16.90
09P	16.00	20.00	13.46	18.90
10P	18.00	22.00	15.46	20.90
11P	20.00	24.00	17.46	22.90
12P	22.00	26.00	19.46	24.90
13P	24.00	28.00	21.46	26.90
14P	26.00	30.00	23.46	28.90
15P	28.00	32.00	25.46	30.90
16P	30.00	34.00	27.46	32.90

燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.				
UNIT	SCALE	SHEET	TITLE:	
mm		1 of 1	2.00mm PITCH 180° WAFER	
B5	EN1001130026	2010.01.13		DRAWN BY
B4	REVISE	2007.05.18		陳耀元
B3	REVISE	2006.05.11		2005.03.03
B2	REVISE	2006.05.07		GENERAL TOLERANCE
B1	REVISE	2005.11.24		X. X±0.25
B0	NEW RELEASE	2005.10.07	X. XX±0.15	
REV.	DESCRIPTION	DATE	X. XXX±0.05	
			ANGLE±	
			▷ ⊕	
			DRAW NO. : A2006WV-XP	
			REV. B5	