CL 222 TM

Six-conductor plug with straight cover


Material · Finish

Part name	Material	Finish
Plug case	Polycarbonate	Clear
Terminal	Phosphor Bronze	Gold plated
Cover	Polycarbonate	Beige

Applicable Cable				
Conductor diameter	Copper foil or AWG#26			
Insulator diameter	0.9~ 1.0			


Electrical Performance

Item	Condition	Specification	
Current rating	Per pin	0.5A	
Voltage rating	Per pin	125V AC	
Insulation Resistance	100V DC	100 M Min.	
Withstanding Voltage	1 minute	500V r.m.s AC	




CL 222 TM

Eight-conductor plug with straight cover




Eight-conductor thin straight plug with cover (For gang-jack)




CL 222 TM

L-shaped 8-conductor plug with cover



T-shaped 8-conductor plug with cover



CL 222 TM

PLUG WIRING TOOL

Jig	Cable Cramp Jig		Terminal Crimping Jig		
Plug	CL No.	Product No.	CL No.	Product No.	
TM11P ^r _J -66P 902		TM11P66P cable crimping	901-0938-4	Applicator 105TM11P-66P	
	902-0132-8	Hand press HOS-7	901-0005-4	Model 105 crimping tool	
TM11P ^r _J -88P	902-0077-1	TM11P88P cable crimping jig	901-0221-0	Applicator 105TM11P-88P	
	902-0132-8	Hand press HOS-7	901-0005-4	Model 105 crimping tool	

PLUG ASSEMBLY DRAWING

