


技术参数 SPECIFICATIONS


- 线数 (Poles) : 2~15(20)
- 适用线规 (Applicable wires) : AWG32#~26#
- 适用基板厚度 (Applicable PC board thickness) : 1.6mm
- 温度范围 (Temperature range) : -25℃~85℃
- 额定电压 (Voltage rating) : 125V.Ac/Dc
- 额定电流 (Current rating) : 1A
- 接触电阻 (Contact resistance) : ≤0.02Ω
- 绝缘电阻 (Insulation resistance) : ≥500MΩ
- 耐压 (Withstand voltage) : 500V.Ac/1min
- 材料 (Material) :
 孔座 (Housing) : 尼龙 (PA66) UL94V-2(0)
 针座 (Wafer) : 尼龙 (PA66) UL94V-2(0)
 端子 (Terminal) : 磷青铜 (Phos. bronze Tin/plated)




端子 TERMINAL (ZH)

型号 Type	适用线规 Applicable wires mm ²	AWG#	电线外径 O.D of wire ins mm	数量 Quantity
HX15000-PT	0.032~0.14	32~26	0.6~1.2	15000PCS/盘

HX15000-PT (ZH)





HX15000-Y (ZH)



安装尺寸 MOUNTING MEASUREMENT

HX15001-WA (ZH)



孔座 HOUSING (ZH)

线数 Poles	型号 Type	尺寸Dimensions(mm)		
		A	B	C
2	HX15000-2Y	1.5	3.4	4.5
3	HX15000-3Y	3.0	4.9	6.0
4	HX15000-4Y	4.5	6.4	7.5
5	HX15000-5Y	6.0	7.9	9.0
6	HX15000-6Y	7.5	9.4	10.5
7	HX15000-7Y	9.0	10.9	12.0
8	HX15000-8Y	10.5	12.4	13.5
9	HX15000-9Y	12.0	13.9	15.0
10	HX15000-10Y	13.5	15.4	16.5
11	HX15000-11Y	15.0	16.9	18.0
12	HX15000-12Y	16.5	18.4	19.5
13	HX15000-13Y	18.0	19.9	21.0
14	HX15000-14Y	19.5	21.4	22.5
15	HX15000-15Y	21.0	22.9	24.0
...
20	HX15000-20Y	28.5	30.4	31.5

针座 WAFER (ZH)

线数 Poles	型号 Type	尺寸Dimensions(mm)		
		直式(180°)	弯式(90°)	A B
2	HX15001-2A	HX15001-2WA	1.5	4.5
3	HX15001-3A	HX15001-3WA	3.0	6.0
4	HX15001-4A	HX15001-4WA	4.5	7.5
5	HX15001-5A	HX15001-5WA	6.0	9.0
6	HX15001-6A	HX15001-6WA	7.5	10.5
7	HX15001-7A	HX15001-7WA	9.0	12.0
8	HX15001-8A	HX15001-8WA	10.5	13.5
9	HX15001-9A	HX15001-9WA	12.0	15.0
10	HX15001-10A	HX15001-10WA	13.5	16.5
11	HX15001-11A	HX15001-11WA	15.0	18.0
12	HX15001-12A	HX15001-12WA	16.5	19.5
13	HX15001-13A	HX15001-13WA	18.0	21.0
14	HX15001-14A	HX15001-14WA	19.5	22.5
15	HX15001-15A	HX15001-15WA	21.0	24.0
...
20	HX15001-20A	HX15001-20WA	28.5	31.5

HX15001-A (ZH)

