


技术参数 SPECIFICATIONS


- 线数 (Poles) : 2~16(28)
- 适用线规 (Applicable wires) : AWG30#~24#
- 适应基板厚度 (Applicable PC board thickness) : 1.2~1.6mm
- 温度范围 (Temperature range) : -25℃~85℃
- 额定电压 (Voltage rating) : 250V.Ac/Dc
- 额定电流 (Current rating) : 2A
- 接触电阻 (Contact resistance) : $\leq 0.02\Omega$
- 绝缘电阻 (Insulation resistance) : $\geq 1000M\Omega$
- 耐压 (Withstand voltage) : 800V.Ac/1min
- 材料 (Material) :
 - 壳体 (Housing) : 尼龙 (PA66) UL94V-2(0)
 - 端子 (Terminal) : 磷青铜 (Phos.bronze Tin/plated)




端子 TERMINAL(JC20)

型号 Type	适用线规 Applicable wires mm ²	AWG#	电线外径 O.D of wire ins mm	数量 Quantity
HX20010-PT	0.05~0.22	30~24	0.9~1.4	10000PCS/盘


HX20010-PT(JC20)



安装尺寸 MOUNTING MEASUREMENT



HX20010-Y(JC20)



壳体 HOUSING(JC20)

极数 Poles	型号 Type	尺寸Dimensions(mm)	
		A	B
2	HX20010-2Y	2.0	4.5
3	HX20010-3Y	4.0	6.5
4	HX20010-4Y	6.0	8.5
5	HX20010-5Y	8.0	10.5
6	HX20010-6Y	10.0	12.5
7	HX20010-7Y	12.0	14.5
8	HX20010-8Y	14.0	16.5
9	HX20010-9Y	16.0	18.5
10	HX20010-10Y	18.0	20.5
11	HX20010-11Y	20.0	22.5
12	HX20010-12Y	22.0	24.5
13	HX20010-13Y	24.0	26.5
14	HX20010-14Y	26.0	28.5
15	HX20010-15Y	28.0	30.5
16	HX20010-16Y	30.0	32.5
...
28	HX20010-28Y	54.0	56.5