



端子 TERMINAL (TJC8A/杜邦带锁)

型号 Type	适用线规 Applicable wires		电线外径 O.D of wire ins	数量 Quantity
	mm ²	AWG#	mm	
HX25418-PT	0.08~0.33	28~22	1.0~1.6	10000PCS/箱

HX25418-PT (TJC8A/杜邦带锁)




HX25418-Y (TJC8A/杜邦带锁)




技术参数 SPECIFICATIONS

- ❑ 线数 (Poles): 2~12(24)
- ❑ 适用线规 (Applicable wires): AWG28#~22#
- ❑ 适应基板厚度 (Applicable PC board thickness): 1.6mm
- ❑ 温度范围 (Temperature range): -25°C~85°C
- ❑ 额定电压 (Voltage rating): 250V.Ac/Dc
- ❑ 额定电流 (Current rating): 3A
- ❑ 接触电阻 (Contact resistance): ≤0.02Ω
- ❑ 绝缘电阻 (Insulation resistance): ≥1000MΩ
- ❑ 耐压 (Withstand voltage): 800V.Ac/1min
- ❑ 材料 (Material):
 孔座 (Housing): 尼龙 (PA66) UL94V-2(0)
 端子 (Terminal): 磷青铜 (Phos.bronze Tin/plated)

HX25418-A (TJC8A/杜邦带锁)



HX25418-WA (TJC8A/杜邦带锁)



孔座 HOUSING (TJC8A/杜邦带锁)

线数 Poles	型号 Type	尺寸 Dimensions(mm)	
		A	B
2	HX25418-2Y	2.54	5.08
3	HX25418-3Y	5.08	7.62
4	HX25418-4Y	7.62	10.16
5	HX25418-5Y	10.16	12.70
6	HX25418-6Y	12.70	15.24
7	HX25418-7Y	15.24	17.78
8	HX25418-8Y	17.78	20.32
9	HX25418-9Y	20.32	22.86
10	HX25418-10Y	22.86	25.40
11	HX25418-11Y	25.40	27.94
12	HX25418-12Y	27.94	30.48
...
24	HX25418-24Y	58.42	60.96

针座 WAFER (TJC8A/杜邦带锁)

线数 Poles	型号 Type	尺寸 Dimensions(mm)	
		A	B
2	HX25418-2A/WA	2.54	7.56
3	HX25418-3A/WA	5.08	10.10
4	HX25418-4A/WA	7.62	12.64
5	HX25418-5A/WA	10.16	15.18
6	HX25418-6A/WA	12.70	17.72
7	HX25418-7A/WA	15.24	20.26
8	HX25418-8A/WA	17.78	22.80
9	HX25418-9A/WA	20.32	25.34
10	HX25418-10A/WA	22.86	27.88
11	HX25418-11A/WA	25.40	30.42
12	HX25418-12A/WA	27.94	32.96
...
24	HX25418-24A/WA	58.42	63.44

安装尺寸 MOUNTING MEASUREMENT

