



技术参数 SPECIFICATIONS

- 适用线规 (Applicable wires) : AWG24#~12#
- 温度范围 (Temperature range) : -20℃~85℃
- 额定电压 (Voltage rating) : 300V.Ac/Dc
- 额定电流 (Current rating) : 18A max
- 接触电阻 (Contact resistance) : $\leq 0.01\Omega$
- 绝缘电阻 (Insulation resistance) : $\geq 1000M\Omega$
- 耐压 (Withstand voltage) : 1500V.Ac/1min
- 材料 (Material) :
 - 壳体 (Housing) : 尼龙 (PA66) UL94V-2 (0)
 - 端子 (Terminal) : 磷青铜 (Phos.bronze Tin/plated)
 - 端子 (Terminal) : 黄铜 (Brass Tin/plated)

端子 TERMINAL

型号 Type	适用线规 Applicable wires		材料 Material	材料厚度 Thickness mm	数量 Quantity
	mm'	AWG#			
HX630N-21T	ST0-21-250N	0.3~0.75 22~18	黄铜 Brass	0.4	7000PCS/包
HX630N-41T	ST0-61-250N	0.75~2.0 18~14		0.4	6000PCS/包
HX630N-61T	ST0-81-250N	2.0~3.5 14~12		0.4	5000PCS/包

型号 Type	适用线规 Applicable wires		材料 Material	材料厚度 Thickness mm	数量 Quantity
	mm'	AWG#			
HX63092-PT	0.52~2.1	20~14	黄铜 Brass	0.35	6000PCS/包
HX50008-01PT	0.22~0.5	24~20		0.3	2000PCS/包
HX50008-21PT	0.75~2.0	18~14		0.3	1500PCS/包
HX630S-61TO	SFPS-61T-240	0.75~2.0 18~14		0.43	4000PCS/包

