



SPECIFICATIONS

Rated Current:3.0AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:1000V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°c to +105°c


Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(Ul94V-0)
 Standard: PBT
 Max.Processing Temp: 180°C for 30-60 seconds
 (200°C for 10 seconds)

Ordering Information

3210 XX S XX X B K00 X 01

- No.of Pins 6--64
- Contact Plating G0:Gold Flash
- Insulator Material Option
- Packing T=Tube A=Tray P=Tube+Cap
- 60:Gold Flash
- G1:3U" Gold
- G2:5U" Gold
- G3:10U" Gold
- G4:15U" Gold
- G5:30U" Gold
- SO:Gold Flash/Tin
- SN:Tin
- A=BK-PBT
- B=BK-PA66
- C=BK-PA6T
- D=BK-PA46
- E=BK-PA9T
- F=BK-LCP

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



A	REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	OPERATION	DRAW	YTYuSheng	15.01.28	SCALE	FIT	PART NO.	TITLE:
	A0	2015.01.28	NEW DRAWING		Angle	±3°		X.XXX	±0.10	CHECK		UNIT	mm	3210XXXXXXBK00X01	2.54mm Box Header H8.8mm 180°
B								X.X	±0.30			SIZE	A4		
C								X.XX	±0.20			SHEET	1/1		
D												PROJ.			
E															
F															
G															

JILIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992