




**SPECIFICATIONS**

Rated Current: 3.0AMP  
 Contact Resistance: 30mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C


Contact Material: Brass  
 Contact Plating: Au or Sn Over Ni  
 Insulator Material: Polyester (UL94V-0)  
 Standard: PBT  
 Max. Processing Temp: 180°C for 30-60 seconds  
 (200°C for 10 seconds)



**Ordering Information**

35112 XX B F R XX BNA1

No. of Pins: 16-64P  
 Contact Type: M=Male, F=Female  
 Contact Plating: G0:Gold Flash, S1:3U" Gold, S2:5U" Gold, S3:10U" Gold, S0:Gold Flash/Tin, SN:Tin



Dimension antitheses list	
ITEM	A
Standard	2.90
Alternate	

OPERATION		DRAW		SCALE		FIT		TITLE:	
OPERATION	DRAW	UNIT	FIT	PROJ.	SHEET	SIZE	SHEET	PART NO.	DATE
X.X	Y.YuSheng	mm	A4	1/1	1/1	A4	1/1	35112XXBFRXXBNA1	2014.09.16
±0.30	14.09.16								
X.XX	CHECK								
±0.20									
X.XXX	APPROVE								
±0.10									
Angle									
±3°									
DIM									
TOL									
CHANGE									
MODIFICATION DESCRIPTION									
NEW DRAWING									
2014.04.11									
2014.09.16									
REV	DATE								

**JILIN** 深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892

欧式插座 母座 90度 2xNPIN 成品系列图