

SPECIFICATIONS

Rated(额定参数): 300V,12A
 Dielectric strength(抗电强度): AC1500V/1 Minute
 Insulation Resistance(绝缘电阻):1000MΩ Min
 Contact Resistance(接触电阻):20mΩ Max
 Screw Torque(扭矩): 0.4Nm (3.5Lb.in)
 Wire Range(线径):1.4~26AWG
 Strip length(剥线长度):5~6mm
 Temp. range(操作温度): -40℃~+105℃
 MAX Soldering(瞬时温度):+250℃,5s

Housing Material(塑件): PA66 (UL94 V-0)
 Contact(端子): Brass, Tin plating(黄铜镀锡)
 Clamp(方块): Brass/Steel(铜/铁), Ni plating(镀镍)
 Screw (螺丝): M2.5, Steel, Zinc plating(钢,镀锌)

IN MM	PITCH RANGE		NOMINAL DIMENSION RANGE		IN MM
	OVER	TO	OVER	TO	
6	10	10	30	60	100
10	24	24	60	100	150
±0.10	±0.15	±0.25	±0.30	±0.50	±0.70
					±1.00

Ordering Information

JL 127 - 508 XX X X 1






Pitch
500=5.0PH
508=5.08PH

No. of pins
2P,3P,4P~24P

Housing Color
B=Black
G=Green
U=Blue
R=Red
W=White
Y=Yellow
O=Orange
E=Grey

Packing
O=Pe
T=Tube
A=Tray

Recommended P.C.B Layout(Top Side)



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	SCALE	FIT	UNIT	SIZE	SHEET	PROU.	TITLE:	PART NO.
A0	2019.06.21	NEW DRAWING		XX ±0.30	Yiyusheng	19.06.21	A4	mm	A4	1/1		JL 127-508XXXX1	
1			CHANGE	X:XX ±0.20									
				X:XXX ±0.10	CHECK								
				Angle ±3°	APPROVE								

JILIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992

5.08mm Terminal Blocks Female