





## SPECIFICATIONS

Rated (额定参数): 300V, 8A  
 Dielectric strength (抗电强度): AC1500V/1 Minute  
 Insulation Resistance (绝缘电阻): 1000MΩ Min  
 Contact Resistance (接触电阻): 20mΩ Max  
 Screw Torque (扭矩): 0.2Nm (1.7Lb.in)  
 Wire Range (线径): 28~16AWG  
 Strip length (剥线长度): 6~7mm  
 Temp. range (操作温度): -40°C~+105°C  
 MAX Soldering (瞬时温度): +250°C, 5s

Housing Material (塑件): PA66 (UL94 V-0)  
 Contact (端子): Phosphor Bronze, Tin plating (磷铜镀锡)  
 Clamp (方块): Brass (黄铜), Ni plating (镀镍)  
 Screw (螺丝): M2.0 Steel, Zinc plating (钢, 镀锌)

PITCH RANGE	NOMINAL DIMENSION RANGE					
	IN MM	OVER	IN MM	OVER	OVER	OVER
TO 6	10	TO 10	30	TO 60	100	OVER 150
TO 10	24	TO 30	60	TO 100	150	OVER 150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70 ±1.00



## Ordering Information

JL15EDGKB-XXX XX G X 1

Pitch: 350=3.5PH, 381=3.81PH  
 No. of pins: 2P, 3P, 4P~24P  
 Housing Color: B=Black, G=Green, U=Blue, R=Red, W=White, O=Orange, E=Grey  
 Pocking: O=Pe, bog, T=Tube, A=Toy

OPERATION	DIM	
	ANGLE	TOL
XX	±0.30	
X.XX	±0.20	
X.XXX	±0.10	
Angle	±3°	

DRAW	BEN	DATE	SCALE	FIT
CHECK	17.01.05		mm	A4
APPROVE			SHEET 1/1	PROU.



深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992

PART NO.: JL15EDGKB-XXXXXXG1  
 TITLE: 3.50/3.81 Pitch Female Pluggable Terminal Blocks

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	APPROVE	DATE	SCALE	FIT	TITLE
A0	2017.01.05	NEW DRAWING			17.01.05	mm	A4	JL15EDGKB-XXXXXXG1
1								3.50/3.81 Pitch Female Pluggable Terminal Blocks