




## SPECIFICATIONS

Rated(额定参数): 300V,8A  
 Dielectric strength(抗电强度): AC1500V/1 Minute  
 Insulation Resistance(绝缘电阻):1000MΩ Min  
 Contact Resistance(接触电阻):20mΩ Max  
 Temp. range(操作温度): -40℃~+105℃  
 MAX Soldering(瞬时温度):+250℃,5s

Housing Material(塑件): PA66 (UL94 V-0)  
 Contact(端子): Brass, Tin plating(黄铜镀锡)

PITCH RANGE		NOMINAL DIMENSION RANGE					
IN MM		IN MM					
TO	OVER	TO	OVER	TO	OVER	TO	OVER
6	10	30	60	100	150	150	150
10	24	30	60	100	150	150	150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70	±1.00



## Ordering Information


JL15EDGVC-XXX XX G X 1

Pitch  
 350=3.5Pth  
 381=3.81Pth

No.of pins  
 2P~24P

Housing Color  
 B=Black  
 G=Green  
 U=Blue  
 R=Red  
 W=White  
 Y=Yellow  
 O=Orange  
 E=Grey

Packing  
 0=Pe bog  
 A=Troy  
 T=Tube



Recommended P.C.B Layout(Top Side)

OPERATION	DRAW		BEN	17.12.22	SCALE	FIT	PART NO.
	UNIT	mm					
X.X	±0.30	CHECK					
X.XX	±0.20						
X:XXX	±0.10						
Angle	±3°	APPROVE					
DIM	TOL						

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	TITLE:
A0	2017.12.22	NEW DRAWING					3.50/3.81mm Pitch Male Pluggable Terminal Blocks
1							



深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992