

SPECIFICATIONS

Rated(额定参数): 300V,1.5A
 Dielectric strength(抗电强度): AC2000V/1 Minute
 Insulation Resistance(绝缘电阻):1000MΩ Min
 Contact Resistance(接触电阻):20mΩ Max
 Temp. range(操作温度): -40℃~+105℃
 MAX Soldering(瞬时温度):+250°C,5s

Housing Material(塑件): PA66 (UL94 V-0)
 Contact(端子): Brass, Tin plating(黄铜镀锡)





PITCH RANGE		NOMINAL DIMENSION RANGE					
IN MM		IN MM		IN MM		IN MM	
OVER	TO	OVER	TO	OVER	TO	OVER	TO
6	10	10	24	30	60	100	150
±0.10	±0.15	±0.25	±0.30	±0.30	±0.50	±0.70	±1.00

Ordering Information

JL2EDGR-XXX XX G X 1

- Pitch
500=5.0PH
508=5.08PH
- No. of pins
2P~24P
- Housing Color
B=Black
G=Green
U=Blue
R=Red
W=White
Y=Yellow
E=Grey
- Packing
0=Pe bag
T=Tube
A=Troy

Recommended P.C.B Layout(Top Side)



REV		DATE		MODIFICATION DESCRIPTION		CHANGE		DIM		TOL		APPROVE		DRAW		BEN		17.01.05		SCALE		FIT		PART NO.		TITLE:	
A0		2017.01.05		NEW DRAWING				X:XXX		±0.10		CHECK								mm		A4		JL2EDGR-XXXXXXG1		5.0/5.08mm Pitch Male Pluggable Terminal Blocks	
1		2		3		4		5		6		7		8		9											

JIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992