


HTP TYPE



ITEN NO.	L	A	C
HTP-306	6.0±0.25	5.5±0.25	M3
HTP-308	8.0±0.25	5.5±0.25	
HTP-310	10.0±0.35	5.5±0.25	
HTP-312S	12.1±0.35	5.5±0.25	
HTP-312	12.7±0.35	5.5±0.25	
HTP-315	15.0±0.35	5.5±0.25	
HTP-318	18.0±0.35	5.5±0.25	
HTP-320	20.0±0.45	5.5±0.25	
HTP-322	22.0±0.45	5.5±0.25	
HTP-325	25.0±0.45	5.5±0.25	
HTP-330	30.0±0.45	5.5±0.25	

承認
KSS
98.10.05
邱平裕

審查

製圖
KSS
98.10.05
謝文通

設計

中文名
六角內螺紋隔離柱

MATERIAL
UL 94V-2
NYLON 66

ITEM NO.
HTP TYPE

SCALE

FINISH

NAME

HEXAGONAL TAPPED SPACER

使用機種

△ (. .)

TOLERANCE
AS FIGURE

△ (. .)
10-05-2009
DATE

REVISIONS
K001

R.NO.



凱士士企業股份有限公司

▶ 請勿實測圖面 ◀