


P.C.B Layout (copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3~20N
 Operating Life:5,000cycles

Model NO	A=φ6	PJ-3136
	A=φ6	PJ-3136A
	A=M6xP0.5	PJ-3136B
Schematic		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.																																																																							
	A		NEW																																																																										
<table border="1"> <tr> <td>② Terminal</td> <td>3</td> <td>Phosphor bronze</td> <td>Au Plating</td> </tr> <tr> <td>① Housing</td> <td>1</td> <td>Nylon</td> <td>Black</td> </tr> <tr> <td>ITEM</td> <td>PART NAME</td> <td>TER.NO.</td> <td>QTY.</td> <td>MATERIAL</td> <td>FINISHING</td> <td>REMARK</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td colspan="2">DATE</td> <td colspan="3">TITLE: PHONE JACKES</td> </tr> <tr> <td colspan="2">DRAWN J.X.Zhang</td> <td colspan="2">2013/11/11</td> <td colspan="3">ELECTRONICS CO.,LTD</td> </tr> <tr> <td colspan="2">CHECKED</td> <td colspan="2"></td> <td colspan="3">PART NO. PJ-3136</td> </tr> <tr> <td colspan="2">APPROVALS</td> <td colspan="2"></td> <td colspan="3">SCALE: 1:1</td> </tr> <tr> <td colspan="2">TOLERANCES ARE</td> <td>30^{+0.15}</td> <td>±0.30</td> <td>ANGLE</td> <td>UNIT: mm</td> <td>PROJ. SHEET 1 OF 1</td> </tr> <tr> <td></td> <td>10^{-0.30}</td> <td>±0.20</td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td>5^{-0.10}</td> <td>±0.15</td> <td>±2°</td> <td></td> <td></td> <td></td> </tr> <tr> <td></td> <td>~5</td> <td>±0.10</td> <td></td> <td></td> <td></td> <td></td> </tr> </table>							② Terminal	3	Phosphor bronze	Au Plating	① Housing	1	Nylon	Black	ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK	APPROVALS		DATE		TITLE: PHONE JACKES			DRAWN J.X.Zhang		2013/11/11		ELECTRONICS CO.,LTD			CHECKED				PART NO. PJ-3136			APPROVALS				SCALE: 1:1			TOLERANCES ARE		30 ^{+0.15}	±0.30	ANGLE	UNIT: mm	PROJ. SHEET 1 OF 1		10 ^{-0.30}	±0.20						5 ^{-0.10}	±0.15	±2°					~5	±0.10				
② Terminal	3	Phosphor bronze	Au Plating																																																																										
① Housing	1	Nylon	Black																																																																										
ITEM	PART NAME	TER.NO.	QTY.	MATERIAL	FINISHING	REMARK																																																																							
APPROVALS		DATE		TITLE: PHONE JACKES																																																																									
DRAWN J.X.Zhang		2013/11/11		ELECTRONICS CO.,LTD																																																																									
CHECKED				PART NO. PJ-3136																																																																									
APPROVALS				SCALE: 1:1																																																																									
TOLERANCES ARE		30 ^{+0.15}	±0.30	ANGLE	UNIT: mm	PROJ. SHEET 1 OF 1																																																																							
	10 ^{-0.30}	±0.20																																																																											
	5 ^{-0.10}	±0.15	±2°																																																																										
	~5	±0.10																																																																											