

REV.	ECN. NO.	APPD.
A		

NOTES:





Current Rating: 3.0AMP
 Contact Resistance: 20mΩ Max
 Insulation Resistance: 1000MΩ Min
 Withstand Voltage: 1000V AC/Minute
 Operation Temperature: -40°C to +105°C

Contact Material: Brass
 Contact plating: Sn or Au Over Ni
 Insulator Material: PBT or PA6T+30%GF(UL94V-0)
 No side slot "A" and "B" from 6 to 16Pin
 No side slot "A" from 18 to 58Pin

Ordering Information

MTE210-XX R X

No. of Pins	Latch Type
06 24	L=Long Latch
08 26	S=Short Latch
10 30	N=Without Latch
12 34	
14 40	
16 50	
18 60	
20 64	



X.	± 0.30	X.°	± 5°	UNITS	mm	NAME(INTENDED USE)	MINTRON CO.,LTD.
X.	± 0.20	X°	± 2°	MATL			
.XX	± 0.10	.XX°	± 1°	FINISH		PART NO.(INTENDED USE)	TITLE: MTE210-XXRL
.XXX	± 0.05	.XXX°	± 0.5°	QTY		APPD: SUNNY	DWG NO.:
EJECTOR HEADER CONNECTOR						CHKD: LISA	SCALE
						DR: ZOE	1/1
						2006-11-28	SHEET
							1/1
							REV.
							A