



NOTES

- ① 材料：TABLE 1 参照
MATERIAL：SEE TABLE 1
- ② 本製品の適応嵌合相手及び各種仕様書はSHEET 2を御参照下さい。
REFER TO SHEET 2 FOR MATE PARTNER AND VARIOUS SPECIFICATION DOCUMENT.
- ③ 極数/2=偶数に適応
APPLICABLE FOR CIRCUIT SIZE/2 = EVEN
- ④ 発注番号：TABLE 2 参照
ORDER No.：SEE TABLE 2


501189 ** **

極数 CIRCUIT SIZE	ハウジングカラー HOUSING COLOR
	10:NATURAL(WHITE)



④ TABLE 2

			ハウジングカラー NATURAL(WHITE)	
25.3	24.0	26.7	501189 5010	50
20.3	19.0	21.7	501189 4010	40
15.3	14.0	16.7	501189 3010	30
10.3	9.0	11.7	501189 2010	20
C	B	A	発注番号 ORDER No.	極数 CIRCUIT SIZE
極数別 寸法 DIMENSION			梱包形態：ポリ袋 PACKAGE:POLYBAG	



① TABLE 1

部品 PART	材質 MATERIAL
ハウジング HOUSING	ポリアミド(PA), UL94V-0, 色：SEE TABLE 2 POLYAMIDE(PA), UL94V-0, COLOR：SEE TABLE 2
DOCUMENT STATUS	P1 RELEASE DATE 2019/09/17 08:20:59

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS mm	SCALE NTS	CURRENT REV DESC:		molex		
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 615136				
ANGULAR TOL	± 3.0 °	DRWN: AISHIKAWA	2019/09/05	PRODUCT CUSTOMER DRAWING		
4 PLACES	± 0.2	CHK'D: AIDA	2019/09/11	DOCUMENT NUMBER		
3 PLACES	± 0.2	APPR: SAKIYAMA	2019/09/17	5011890000-SD		
2 PLACES	± 0.2	INITIAL REVISION:		DOC TYPE	DOC PART	REVISION
1 PLACE	± 0.2	DRWN: AISHIKAWA	2019/03/22	PSD	000	B
0 PLACES	± 0.2	APPR: KOMURAKAMI	2019/04/03	SHEET NUMBER		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER
			A3-SIZE	501189	SEE SHEET 2	1 OF 2

△ 2 適応製品及び各種仕様書
APPLICABLE PRODUCTS AND VARIOUS SPECIFICATIONS

梱包仕様書 PACKING SPECIFICATION	SPECIFICATION NUMBER SPK-501189-001
--------------------------------	--

適応圧着端子 APPLY CRIMP TERMINAL	PART NUMBER		PLATING TYPE		WIRE SIZE(AWG) #28 - #32
	501193 7000	501193 8000	GOLD (THICKNESS) 【MICRO-METER MIN.】	0.1	
	501193 9000	0.38			
	0.76				

列 ROW	DUAL					
	SMT					
	VERTICAL			RIGHT ANGLE		
	GOLD (THICKNESS) 【MICRO-METER MIN.】			GOLD (THICKNESS) 【MICRO-METER MIN.】		
適応嵌合相手 MATE WITH	0.1	0.38	0.76	0.1	0.38	0.76
シリーズ番号 SERIES No.	501190	203564	203565	202396	203566	203567
製品仕様書 PRODUCT SPECIFICATION	5011890000-PS 001					
取扱説明書 APPLICATION SPECIFICATION	5011890000-AS 000					

製品嵌合図は各"適応嵌合相手"図面参照のこと
 MATING VIEW:REFER TO EACH "MATE WITH" PART DRAWING.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
DIMENSION UNITS	SCALE	CURRENT REV DESC:				molex				
mm	NTS									
GENERAL TOLERANCES (UNLESS SPECIFIED)		EC NO: 615136 DRWN: AISHIKAWA 2019/09/05 CHK'D: AIDA 2019/09/11 APPR: SAKIYAMA 2019/09/17 INITIAL REVISION: DRWN: AISHIKAWA 2019/03/22 APPR: KOMURAKAMI 2019/04/03				PICO-CLASP 1.0 W/B DUAL ROW REC HSG				
ANGULAR TOL	± 3.0 °					PRODUCT CUSTOMER DRAWING				
4 PLACES	± 0.2					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
3 PLACES	± 0.2					5011890000-SD		PSD	000	B
2 PLACES	± 0.2					MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
1 PLACE	± 0.2	SEE SHEET 2				2 OF 2				
0 PLACES	± 0.2									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
			A3-SIZE	501189						