

NOTE
 MATERIAL & FINISH
 HOUSING : PBT 30%GF (UL94 V-0)
 CONTACT: PHOSPHOR BRONZE, Au OR Sn
 OVER NI
 CABLE INSULATION: UL 2651,GREY RED SIDE
 CONDUCTOR: 28AWG(7/0.12mm)
 ELECTRICAL: 300V

ELECTRICAL & MECHANICAL
 CURRENT RATING: 1.0A
 CONTACT RESISTANCE: 1.0Ω MAX.
 INSULATION RESISTANCE: 5MΩ MIN.
 WITHSTAND VOLTAGE: 300V DC 10S
 THE CABLE ASSEMBLY MUST 100% TEST

PART NO.

Z-S11F0 ** * * ** 0


No. of Pins
 04P~64P

LENGTH OF
 LINE(mm)
 100=100mm
 200=200mm

PLATING
 1=GOLD FLASH
 4=GOLD 10U"
 5=GOLD 15U"
 6=GOLD 30U"
 7=GOLD FLASH/NI
 A=GOLD 10U"/NI
 B=GOLD 15U"/NI
 C=GOLD 30U"/NI
 T=TIN

Color Insulator
 B=Black
 G=Grey 427C

CONNECT METHOD



②	CONN.	2.54 IDC XXP PBT Black material: XX,Plating Xu" Gold	2	SET
①	WIRE	UL2651 PH1.27mm XXP 28AWG(7/0.12TC) PVC Grey Marking Red Side	XXXX	MM
NO.	NAME	TITLE	QTY	UNIT

UNITS <input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH	
GENERAL TOLERANCES: (UNLESS SPECIFIED)	
	mm INCH
4 PLACE	± ** ±. **
3 PLACE	± 0.15 ±. **
2 PLACE	± 0.25 ±. **
1 PLACE	± 0.40 ±. **
ANGULAR:	X° ± ** X° ± 3°

NAME: 2.54mm IDC SOCKET (WITH CABLE)
PART NO: Z-S11F0*****0
APPD: 楊海文 1/4'16
CHKD: 廖小瓊 1/4'16
DRAWN: 陳惠枝 1/4'16

nextron NEXTRONICS ENGINEERING CORP.	
TITLE: CUSTOMER DWG	
DWG NO: 010-0000-F11	C
SCALE: 1/1	SHEET: 1/1
REV.: A	

A	NEW RELEASED	1/4'16	楊海文
REV.	DESCRIPTION	DATE	APPD