

WJ127-5.0
WJ127-5.08



Pitch 5.0mm 5.08mm
Poles 2p/3p~24p
Number of poles

Screws (螺丝)	:M2.5 steel Zinc plated
Wire guard (簧片)	:
Pin header (焊针)	:Brass, Tin plated
Housing (塑件)	:PA66, UL94V-0
Rated voltage (额定电压)	:300V
Rated current (额定电流)	:12A
Contact resistance (接触电阻)	:20mΩ
Insulation resistance (绝缘电阻)	:5000MΩ/DC1000V
Withstanding Voltage (耐电压)	:AC2000V/1Min
Wire range (使用线径)	:26-14AWG 1.5mm ²
Temp.Range (温度范围)	:-40°C~+105°C
Torque (扭矩)	:0.4Nm(3.6lb.in)
Strip length (剥线长度)	:5-6mm

