



Poles: 2P, 3P-24P
Pitch: 5.0mm

Voltage Rating: 300V
Current Rating: 10A
Wire range: 24-12AWG 2.5mm²
Housing: PA66 (UL 94V-0)
Solder Pin: Brass, Tin Plated
Screw: M2.5, Steel (A3), Zinc Plated
Cage: Brass, Nickel Plated
Torque: 0.4N.m

2	5.75改为5.7	王传东	2010.6.19
1	3.4±0.2改为4.0	王传东	2010.6.19
序号/revno.	更改记录/revision record	签名/signature	日期/date

设计/Designed by	绘图/Drawn by	审核/checked by	批准/Approved by	公差/General Tolerance
				x: ±0.2 x.° ±2°
		图名/Title	文件编号/Title No.	.x ±0.1 .x° ±1°
		XY103	页序/Sheet	.xx ±0.05 .xx° ±0.5°
		备注/Remark		.xxx ±0.01
				单位/units: 毫米



新莱亚电子
 XINLEIYA ELECTRONIC CO., LTD