



300V 20A 26-12AWG 2.5mm²
 Poles: 2P&3P-24P
 Pitch: 5.0mm (.197")/5.08mm (.200")

Materials
 Housing: PA66 (UL 94V-0)
 Wire Cage: Brass, Nickel Plated
 Solder Pin: Brass, Tin Plated
 Screw: M3.0, Steel (A3), Zinc Plated
 Torque: 0.5N.m

序号/Rev.No. 更改记录/Revision note 签名/Signature 日期/Date

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance
				X: ±0.2 X: ±0.1 .XX ±0.05 .XXX ±0.01
图名/Title		文件编号/FILE NO.		X: ±2° X: ±1°
XV129VB-5.0		XV129VB-5.08		.XX ±0.5° .XXX ±0.5°
页序/Sheet		备注/Remark		单位/Units: mm

新莱亚电子
 XINLAIYA ELECTRONIC CO., LTD