


300V 8A 28-16AWG 1.5mm²
 Poles: 2P-24P
 Pitch: 3.5mm(.138")/3.81mm(.150")

Materials

Housing: PA66(UL 94V-0)
 Clamp: Phosphor Bronze,Nickel Plated.
 Wire Cage: Brass,Nickel Plated.
 Screw: M2,Steel(Q235),Zinc Plated.

设计 / Designed by	绘图 / Drawing by	审核 / Checked by	批准 / Approved by	未注公差 General Tolerance	
				X	± 0.2
				X	± 0.1
				XX	± 0.05
				XXX	± 0.01
 新莱亚电子科技 XINLAIYA ELECTRONIC CO.,LTD		图名 / Title	文件编号 / File No.	X'	± 2'
		XY2500FF/FE	页序 / Sheet	X''	± 1'
		备注 / Remark		XXX'	± 0.5'
				单位 / Units	mm