

300V 15A

Poles: 2P-24P


Pitch: 5.0mm(.197"),5.08mm(.200")

Materials

Housing: PA66(UL 94V-0)

Solder Pin: Brass, Tin Plated.

序号/Revno.	更改记录/Revision note	签名/Signature	日期/Date
-----------	--------------------	--------------	---------

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance
				X: ±0.2 .X: ±0.1 .XX: ±0.05 .XXX: ±0.01
 XINMATAIYA ELECTRONIC CO., LTD		图名/Title	文件编号/FILE NO.	X: ±2° .X: ±1° .XX: ±0.5° .XXX: ±0.2°
		XY2500R-A X12500R-C	页序/Sheet	单位/Units: mm
备注/Remark				