



序号/Rev.No.	名称/Title	文件编号/File No
1	XY2500VT主体	
2	XY2500RT端子	



125V 4A

Poles: 2-24P

Pitch: 2.5mm


Materials

Housing: PA66 (UL 94V-0)

Solder Pin: Brass, Tin Plated.

Undimensioned tolerances:

Pitch range in mm		Nominal dimension range in mm						—	∩	□
0	Over 6	Over 10	Over 24	Over 30	Over 60	Over 100	Over 150	0.1/10	≤	
T0	T0	T0	T0	T0	T0	T0	T0			
6	Over 10	Over 24	Over 30	Over 60	Over 100	Over 150	Over 150			
±0.10	±0.15	±0.20	±0.25	±0.40	±0.50	±0.70	±1.0	±2°		



设计/Designed by

绘图/Drawing by

审核/Checked by

批准/Approved by

未注公差
General Tolerance

图名/Title

文件编号/File No.

X.
.X°
.xxx
.xx°

2500RT-2.5

QJ/XYT-1003000-00-00

产品图

页序/Sheet

备注/Remark

单位/units: mm



新莱亚电子科技

XINLIYA ELECTRONIC CO.,LTD