


300V 15A  
 Poles: 2P-24P  
 Pitch: 5.0mm(.197"),5.08mm(.200")

### Materials

Housing: PA66(UL 94V-0)  
 Solder Pin: Brass, Tin Plated.

序号/Revno. 更改记录/Revision note 签名/Signature 日期/Date

设计/Designed by	绘图/Drawing by	审核/Checked by	批准/Approved by	未注公差 General Tolerance
				X: ±0.2 .X: ±0.1 .XX: ±0.05 .XXX: ±0.01
 <b>新莱亚电子</b> XINLATA ELECTRONIC CO., LTD		图名/Title	文件编号/File No.	X: ±2° .X: ±1° .XX: ±1° .XXX: ±0.5°
		XY2500V-A XY2500V-C	页序/Sheet	
备注/Remark				单位/Units: mm