



300V 15A
 Poles: 2-22P
 Pitch: 5.0mm (.197")/5.08mm (.200")

Materials

Housing: PA66 (UL 94V-0)
 Solder Pin: Brass, Tin Plated

序号/Rev.No. 更改记录/Revision note

签名/Signature

日期/Date

设计/Designed by

绘图/Drawing by

审核/Checked by

批准/Approved by

未注公差
 General Tolerance

图名/Title

文件编号/File No.

X. ° ±2°
 .X ° ±0.1°
 .XX ±0.05°
 .XXX ±0.01°

XY2500VB-5.0
 XY2500VD-5.08

页序/Sheet

备注/Remark

单位/units: mm



XINLAIYA ELECTRONIC CO., LTD