



300V 7A 24-18AWG 1.0mm²
Poles: 2P, 3P-24P
Pitch: 3.81mm (.150")

Materials

Housing: PA66(UL 94V-0)
 Spring: Phosphor Bronze
 Solder Pin: Brass, Tin Plated
 Screw: M2, Steel (A3), Zinc Plated
 Torque: 0.2N.m

| | | | | | |
|----------------|-------------|---------------|----------------|--|----------------|
| 设计/Designed by | 绘图/Drawn by | 审核/Checked by | 批准/Approved by | 备注/Remarks | |
| | | | | 图名/Title | 文件编号/Title No. |
| | | | | XY340V | 页序/Sheet |
| | | | | 备注/Remark | 单位/Unit |
| | | | | 未注公差 General Tolerances 未注公差 未注公差 未注公差 未注公差 | |