




贴片保险丝(快断型)

SMD Fuse (Fast-Acting) 125V



测试标准:

Testing Standard:
UL248-1 UL248-14

额定分断能力:

Interrupting Rating:
50 Amperes at 125V AC/DC

工作温度:

Operating Temperature:
-55°C ~ +125°C

材料:

Materials:
Substrate:ceramic/glass cover
Termination:sliver over-plated with nickel and tin
Element:silver


焊接方法:

Soldering Method:
Reflow soldering: 260°C, 10s max

包装:

Packaging:
Automaton taped 3000PCS per roll,
90000PCS per carton

Time-Current Characteristics
电流-时间曲线图



电气特性: Electrical Characteristics

额定电流 Ampere Rating	额定电流的% % of Ampere Rating	熔断时间 Opening Time
250mA~1.5A	100%	4 hours Min(大于4小时)
250mA~1.5A	250%	5 s Max(小于5秒)

目录编号: Catalog No.B:125V

目录编号 Catalog No.	额定电流 Ampere Rating	额定电压 Voltage Rating	标示 Marking	熔化热能 ^{1,2} Melting Integral (A ² .S)	认证 Approvals
					● 表示已获认证 ● 表示认证中
12B0250B	250mA	125V	.25	0.0035	●
12B0375B	375mA	125V	E	0.0011	●
12B0500B	500mA	125V	0.5	0.0020	●
12B0750B	750mA	125V	.75	0.0053	●
12B1100B	1A	125V	1	0.0062	●
12B1125B	1.25A	125V	▲	0.022	●
12B1150B	1.5A	125V	1.5	0.028	●