



RECOMMENDED PCB LAYOUT

(PCB THK=1.0~1.6)
 TOLERANCES ARE NON-CUMULATIVE: ±0.05

LDC		JUST		REVISIONS			
P	LR	A		DESCRIPTION	DATE	BY	APP'D
				INITIAL VERSION			MS

- NOTE:
1. MATERIAL SPECIFICATION:
 1.1 HOUSING: NYLON66 UL94 V-0, COLOR : NATURAL.
 1.2 PIN: COPPER ALLOY SQ1.14.
 2. FINISH:
 - PIN: BRIGHT TIN PLATED
 3. ROHS COMPLIANT.
 4. BILL OF PART NO:

P/N	POS	A	B	C
1-2834290-1	2	5.30	7.92	3.96
1-2834290-2	3	9.26	11.88	7.92
1-2834290-3	4	13.22	15.84	11.88
1-2834290-4	5	17.18	19.80	15.84
1-2834290-5	6	21.14	23.76	19.80
1-2834290-6	7	25.10	27.72	23.76
1-2834290-7	8	29.06	31.68	27.72
1-2834290-8	9	33.02	35.64	31.68
1-2834290-9	10	36.98	39.60	35.64
2-2834290-1	11	40.94	43.56	39.60
2-2834290-2	12	44.90	47.52	43.56
2-2834290-3	13	48.86	51.48	47.52

THIS DRAWING IS A CONTROLLED DOCUMENT.

DESIGNED BY: MING.S.18/MAR2017
 CHECKED BY: YANG.X.18/MAR2017
 DRAWN BY: YANG.X.18/MAR2017
 DATE: 108-13/28/17
 PART NUMBER: 114-13/28/17
 VERSION: -

DATE: A4 00779
 SCALE: 1:1
 SHEET: 1 OF 1
 REV: A

WTB 3.96MM PITCH R/A DIP TYPE.

TE Connectivity

NOTE 1