


HSF

NOTES:

Rated Current: 2.0AMP.
 Contact Resistance: 20mΩ Max.
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min.
 Operation Temperature: -40℃ to +125℃(GOLD)
 -40℃ to +105℃(TIN) Δ

Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: PA9T+33%G.F UL94V-0 BK


Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE±0.05)



Ordering Information

1215-12 XX XX M XXX C R XX Δ

No. of Pins Per Row: 02-40	Contact Plating	Pin Length L=B+D+1.5+ $\frac{W^2}{2}$	Insulator Material	Packing	Series No.
G0=Gold Flash	Standard: 058=5.8	C=PA9T	P=Tube	01-99	
G3=10u"Gold	068=6.8	R=Tape&Reel+CAP	P=Tube+CAP		
G4=15u"Gold	078=7.8				
G5=30u"Gold					
S0=Gold Flash/Tin					
S3=10u"Gold/Tin					
S4=15u"Gold/Tin					
S5=30u"Gold/Tin					
SN=Tin					
SM=Matte Tin					



Item	Pin Length	W	E	B	Mating
Standard	5.80	6.50	2.10	2.00	2220T 2221 2227T 2228
	6.80	6.50	2.10	3.00	2235
	7.80	6.50	2.10	4.00	2240 2243 2263 2272
Alternate					

PIN	2-15P	16-25P	26-40P
M	0.10	0.15	0.20

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	Fit	PART NO.
A2	2018/09/07	Modify	Δ	x.X ±0.40	Dwg	2018/09/07	UNIT	mm	1215-12XXXXMXXXCRXX Δ
A1	2018/01/18	Modify P/N	Δ	x.XX ±0.25	CHECK	DATE	SIZE	A4	TITLE:
A0	2012/04/18	NEW	-----	x.XXX ±0.15	APPROVE	DATE	SHEET	1/1	PH2.00 DUAL ROW SMT H=1.5
				Angle ± 3°			PROJ.		Customer NO.
				DIM TOL					

WCON
 Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: salesks@wcon.com