



# HSF

NOTES:  
 Current Rating: 3.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40℃ to +125℃(GOLD)  
 -40℃ to +105℃(TIN)

Contact Material: Phosphor Bronze  
 Contact plating: Au Or Sn over Ni  
 Insulator Material: PA9T+33%G.F UL94V-0



Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



## Ordering Information

2135 - 1 XX M XX CUN X X

- No. of Pins per ROW: 02-40PIN
- Contact Plating: G0=Gold Flash, G3=10μ"Gold, G4=15μ"Gold, G5=30μ"Gold, S0=Gold Flash/Tin, S3=10μ"Gold/Tin, S4=15μ"Gold/Tin, S5=30μ"Gold/Tin, SN=Tin, SM=Matte Tin
- Packing: T=Tube, P=Tube+CAP, R=Tape&Reel+CAP
- Series No. 1=TYPE 1, 2=TYPE 2



PIN	2-15P	16-25P	26-40P
M	0.10	0.15	0.18

Item	Pitch	Mating
Standard	2.54	1115/1120/1125
Alternate		

TITLE	PART NO.	SPEC.
TYPE 1	2135-1XXMXXCUNX1	DUAL/ODD PINS
TYPE 2	2135-1XXMXXCUNX2	DUAL PINS

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A2	2018/08/18	ADD 1*2P-1*3P CAP; MODIFY DRAWING	-----	x.x ±0.40	Surong Xu	2018/08/18	UNIT mm		SEE TABLE
A1	2018/05/07	MODIFY CAP ; ADD DIM.	-----	x.xx ±0.25	CHECK	DATE	SIZE A4		TITLE: FH2.54mm SINGLE ROW 180°SMT H=3.5
A0	2012/08/02	NEW	-----	x.xxx ±0.15	APPROVE	DATE	SHEET 1/1		Customer NO.
				Angle ± 3°			PROJ.		
				DIM TOL					

**WCON**  
 Http: www.wcon.com  
 WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com  
 WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: sales@wcon.com