



# HSF

**NOTES:**

Current Rating: 2.0AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 500V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40℃ to +125℃(Au)  
 -40℃ to +105℃(Sn)  
 Contact Material: Phosphor Bronze  
 Contact plating: Au over Ni  
 Insulator Material: PA9T+33%G.F UL94V-0

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



2\*2P~2\*4P

## Ordering Information


2220T-2 XX M XX CUN X X

No. of Pins per Row: 02~40Pin


Contact Plating:  
 G0=Gold Flash  
 G3=10μ"Gold  
 G4=15μ"Gold  
 G5=30μ"Gold

Packing:  
 T=Tube  
 P=Tube+CAP  
 R=Tape&Reel+CAP

Series No.  
 1=Type 1  
 2=Type 2



SECTION B-B



TYPE 1 W/O POST

TYPE 2 WITH POST

SECTION A-A

Item	Pitch	Mating
Standard	2.00	1215/1220
Alternate		

PIN	2-15P	16-25P	26-40P
M	0.10	0.15	0.18

TITLE	PART NO.
TYPE 1	2220T-2XXMXXCUNX1
TYPE 2	2220T-2XXMXXCUNX2

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW XSR	DATE	SCALE	FIT	PART NO.
A2	2019/01/16	Modify drawing&CAP	-----	x.x ±0.40	CHECK	2019/01/16	UNIT	mm	SEE TABLE
A1	2012/10/29	Modify drawing	-----	x.xx ±0.25	CHECK	DATE	SIZE	A4	TITLE: FH2.00mm DUAL ROW 180°SMT H=2.0
A0	2012/07/12	NEW	-----	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	Customer NO.
				Angle ± 3°			PROJ.		
				DIM TOL					

**WCON**  
 Http: www.wcon.com

WCON-Dongguan  
 Tel: +86 769 85358920  
 Fax: +86 769 85358915  
 E-mail: sales@wcon.com

WCON-Kunshan  
 Tel: +86 512 57468408  
 Fax: +86 512 57468468  
 E-mail: salesks@wcon.com