


# HSF

### NOTES:




Current Rating: 3AMP  
 Contact Resistance: 20mΩ max  
 Withstand Voltage: 500V AC/DC  
 Insulation Resistance: 1000MΩ min  
 Operation Temperature: -55°C to +105°C

Contact Material: Brass  
 Contact plating: Au or Sn Over Ni  
 Insulator Material: PBT+30%G.F.(UL94V-0)

Recommended P.C.B Layout(Top Side)  
 (PCB BOARD TOLERANCE±0.05)



SCALE 1:3



## Ordering Information

3113-XX S XX B K00 X 1

No. of Pins: 10P 30P, 14P 34P, 16P 40P, 20P 50P, 24P 60P, 26P 64P  
 Contact Plating: SP=Gold Flash/Tin, S3=10u"Gold/Tin, S4=15u"Gold/Tin, S5=30u"Gold/Tin  
 Color Insulator: B=Black  
 Packing: A=Tray, T=Tube

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.	TITLE:	WCON-Dongguan	WCON-Kunshan
A2	15/03/30	Modify Drawing		X.X	William Chen	15/03/30	mm	A4	3113-XXSXXBK00X1	2.54Pitch Box Header	Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	Tel: +86 512 57468408 Fax: +86 512 57468488 E-mail: sales@wcon.com
A1	11/12/22	add DIM		X.XX	CHECK		mm	A4				
A0	11/06/16	NEW		X.XXX	APPROVE		mm	1/1				
				Angle ± 3°					Customer NO.			