



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)

NOTES:  
 Current Rating: 1.75AMP  
 Contact Resistance: 20mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 5000MΩ Min  
 Operation Temperature: -55°C to +125°C



Contact Material: Brass  
 Contact plating: Au Or Sn over Ni  
 Insulator Material: LCP+30%G.F UL94V-0

# Ordering Information

3231-XX S XX B S T 1

- No.of Pins      Contact Plating      Insulator Color      Packing
- 06 26            G0=Gold Flash            B=Black            T=Tube
- 08 30            G3=10u"Gold
- 10 34            G4=15u"Gold
- 14 40            G5=30u"Gold
- 16 44            S0=Gold Flash/Tin
- 20 50            S3=10u"Gold/Tin
- S4=15u"Gold/Tin
- S5=30u"Gold/Tin
- SN=Tin

Item	Pitch	Mating
Standard	1.27	5232
Alternate		



OPERATION		DRAW		DATE		SCALE		PART NO.	
XX		JYHuang		2012/09/28		mm		3231-XXXXXXBST1	
X.XX		CHECK		DATE		A4		TITLE:	
X.XXX		± 0.15		± 3'		APPROVE		1.27 Ejector Header "S" Type 180°	
ANGLE		DIM		TOL		PROJ.		Customer NO.	
REV		DATE		MODIFICATION DESCRIPTION		CHANGE		Customer NO.	
A0		2012/09/28		NEW		---		Customer NO.	



Http: www.wcon.com  
 WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com  
 WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: sales@wcon.com