


# HSE

**NOTES:**

Rated Current: 1.75AMP  
 Contact Resistance: 20mΩ max  
 Withstand Voltage: 500V AC/DC  
 Insulation Resistance: 5000MΩ min  
 Operation Temperature: -55°C to +125°C

Contact Material: Brass  
 Contact Plating: Au or Sn Over Ni  
 Insulator Material: CP+30%GF UL94V-0

Recommended P. C. B Layout (Top Side)  
 (PCB BOARD TOLERANCE ± 0.05)



## Ordering Information

3231-XX M XX B S T 2

- No. of Pins: 06, 26, 08, 30, 10, 34, 14, 40, 16, 44, 20, 50, 24
- Contact Plating: G0=Gold Flash, G3=10μ"Gold, G4=15μ"Gold, G5=50μ"Gold, S3=10μ"Gold/Tin, S4=15μ"Gold/Tin, S5=50μ"Gold/Tin, SN=Tin
- Insulator Color: B=Black
- Packing: T=Tube, P=Tube+CAP, R=Tube+Reel+CAP

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.	TITLE:	WCON-Dongguan	WCON-Kunshan
A3	2012/08/31	Modify CAP	△4	XX	△40	2012/08/31	mm	A4	3231-XXMXXBST2	1.27 Ejector Header	Tel: +86 769 85358920	Tel: +86 512 57468408
A3	2012/05/30	Modify drawing		XX	△025		inch	A4		"S" Type SMT With fork	Fax: +86 769 85358915	Fax: +86 512 57468468
A2	2010/08/09	Modify drawing		XXXX	△015						E-mail: sales@wcon.com	E-mail: sales@wcon.com
A0	2009/11/21	NEW		Angle	± 3'							
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	DATE	PROJ		Customer NO.			



WCON-Dongguan  
 Tel: +86 769 85358920  
 Fax: +86 769 85358915  
 E-mail: sales@wcon.com

WCON-Kunshan  
 Tel: +86 512 57468408  
 Fax: +86 512 57468468  
 E-mail: sales@wcon.com