


HSF

NOTES:
 Current Rating: 1.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C

Contact Material: Phosphor Bronze
 Contact plating: Sn over Ni
 Insulator Material: LCP+30%G.F UL94V-0

Recommended P.C.B Layout (Top Side)
 (PCB BOARD TOLERANCE ±0.05)



Ordering Information

3901-XX MM XX D W B X 1

No. of Pins	Contact Plating	Insulator	Color	Packing
04 16	SM=Matte Tin	D=LCP	B=Black	T=Tube
06 18				R=CAP+Reel
08 20				
10 22				
12 24				
14 26				

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A3	2018/05/15	Picoflex Connector--1.27mm SPC Connector	△	OPERATION	Ding	2018/05/15	UNIT	mm	3901-XXMMXXDWBX1
A2	2016/11/01	Modify CAP	△	x.X ±0.40	CHECK		SIZE	A4	TITLE: △ 1.27mm SPC Connector SMT With Peg
A1	2012/12/18	Modify Drawing	△	x.XX ±0.25	APPROVE		SHEET	1/1	Customer NO.
A0	2012/11/01	NEW	----	x.XXX ±0.15			PROJ.		
				Angle ± 3'					
				DIM TOL					



Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com
---	--