

HSF

NOTES:

Current Rating: 1.0AMP
 Contact Resistance: 20mΩ Max
 Withstand Voltage: 500V AC/DC
 Insulation Resistance: 1000MΩ Min
 Operation Temperature: -40°C to +105°C


Contact Material: Phosphor Bronze
 Contact plating: Au Or Sn over Ni
 Insulator Material: PBT+30%G.F UL94V-0

Ordering Information

5225-XX UP XX B X 0 1

No. of Pins Contact Plating Bump
 06P 24P S0=Gold Flash/Ni N=W/O Bump
 08P 26P S3=10u"Gold/Ni W=With Bump
 10P 30P S4=15u"Gold/Ni Color Insulator
 12P 34P S5=30u"Gold/Ni B=Black
 14P 36P SN=Tin G=Grey(427C)
 16P 40P
 20P 44P
 22P 50P

Item	Pitch	Mating
Standard	2.00	3124/3221
Alternate		



REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A1	2013/12/09	1.50±0.20--1.70±0.20	△	X.XX	JYHuang	2013/12/09	UNIT	mm	5225-XXUPXXBX01
A0	2012/10/10	NEW		X.XXX	CHECK	DATE	SIZE	A4	TITLE: 2.00mm IDC SOCKET ("S" TYPE)
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	± 3'	APPROVE	SHEET	1/1	Customer NO.
				DIM	TOL		PROJ.		

WCON

Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: sales@wcon.com