

# HSF



NOTES:  
 Rated Current: 1.0AMP  
 Contact Resistance: 30mΩ max  
 Withstand Voltage: 500V AC/DC  
 Insulation Resistance: 1000MΩ min  
 Operation Temperature: -40℃ to +105℃

Contact Material: Phosphor Bronze  
 Contact Plating: Au Over Ni  
 Insulator Material: PBT+30%G.F UL94V-0


## Ordering Information

5226 - XX YP XX B W 01




- Two Parts Conn+Cover
- No. of Pins 6P-50P
- Contact Plating  
 G0=Gold Flash  
 G3=10u"Gold  
 G4=15u"Gold  
 G5=30u"Gold  
 S0=Gold Flash/Ni  
 S3=10u"Gold/Ni  
 S4=15u"Gold/Ni  
 S5=30u"Gold/Ni
- Color Insulator  
 B=Black  
 G=Grey(427C)



SINGLE RAMP LOCKING ONLY  
 (APPLICABLE FOR 6 TO 12 CKT)



POLARIZATION AND RAMP LOCKING  
 (APPLICABLE FOR 14 TO 50 CKT)



SR P/N: G5226-XXDX01

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.
A2	2018/05/29	MODIFY	---	x.x ±0.40	Ding	2018/05/29	UNIT	mm	5226-XXYPXXBW01
A1	2012/07/28	MODIFY	---	x.xx ±0.25	CHECK	DATE	SIZE	inch	
A0	2010/09/28	NEW	---	x.xxx ±0.15	APPROVE	DATE	SHEET	1/1	TITLE: 2.00mm IDC SOCKET "M" TYPE (WITH RAMP LOCKING)
				Angle ± 3'			PROJ.		Customer NO.
				DIM TOL					

**WCON**  
 Http: www.wcon.com

WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com  
 WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com