






环保物料

TEL: 0769-82001899




SPECIFICATIONS

Voltage rating: 250V AC, DC
 Current rating: 3A, AC, DC
 Withstanding Voltage: 1000V AC/minute
 Insulation resistance: 1000M min
 Temperature range: -25 °C ~ +85 °C
 Contact resistance: 10m max
 Housing Material: LCP UL94V-0
 Pin Material: Brass
 Contact Area Plating: Tin-Plated



Type	Dimension mm					Type	Dimension mm				
	A	B	C	D	E		A	B	C	D	E
2	2.50	10.00	5.95			10	22.50	30.00	25.95	20.80	19.50
3	5.00	12.50	8.45	3.30	2.50	11	25.00	32.50	28.45	23.30	22.00
4	7.50	15.00	10.95	5.80	4.50	12	27.50	35.00	30.95	25.80	24.50
5	10.00	17.50	13.45	8.30	7.00	13	30.00	37.50	33.45	28.30	27.00
6	12.50	20.00	15.95	10.80	9.50	14	32.50	40.00	35.95	30.80	29.50
7	15.00	22.50	18.45	13.30	12.00	15	35.00	42.50	38.45	33.30	32.00
8	17.50	25.00	20.95	15.80	14.50	16	37.50	45.00	40.95	35.80	34.50
9	20.00	27.50	23.45	18.30	17.00	-	-	-	-	-	-



AO	MODIFICATION	DRAW	DATE	TOLERANCE UNLESS OTHERWISE	DRAWN	CK tan
VER				X. ±0.30 X° ±5°	CHKD	
				.X ±0.20 .X° ±2°	APPD	
				.XX ±0.08 .XX° ±1°	VIEW	
				.XXX ±0.03 .XXX° ±0.5°		

XFCN 兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.		SHEET	1/1
		DATE	2010. 4. 12
PRODUCT NAME	2.50mm Crimp Style Connectors	UNITS	mm
PART. NO.	M2501VSF-XX-LP	SCALE	1:1
		DWG. NO.	009