



MODEL CODE

SS-25D01-X

L (mm)  
2~10

SCHMATIC (SHORTING)



P.C.B LAYOUT  
BOTTOM VIEW

RATING	0.3A 50V DC
CIRCUIT	1P2T
CONTACT RESISTANCE	100mΩ MAX.
TRAVEL	2mm
OPERATING FORCE	250±100gf
OPERATING LIFE(cycles)	10,000

REVISIONS					UNSPECIFIED TOLERANCES		DSND	DATE	SCALE: N/A	MODEL TYPE: SLIDE SWITCH		
Δx					ANGULAR	±5°	DWN	DATE	VIEW:	PART NO.: SS-25D01		
Δx					L ≤ 4	±0.2	CHKD	DATE	UNIT: mm	DWG NO.: SS-25D01-X		
Δx					4 < L ≤ 16	±0.3	APPD	DATE	SIZE: A4	WEIGHT		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	XKB INDUSTRIAL PRECISION CO., LIMITED			1.0g	SHEET	REVISION
					L > 63	±0.5				1/1	A0	