






RoHS



OPERATING FORCE	
CODE	VIGOR
B1	120±30gf
B2	180±30gf
B3	250±30gf

PCB Layout(Pattern side)



TOTAL HEIGHT					
CODE	H	∅	CODE	H	∅
A1	1.5	2.0	A9	3.0	2.0
A2	1.6	2.0	A10	3.5	2.0
A3	1.7	2.0	A11	3.7	2.0
A4	1.8	2.0	A12	4.0	2.0
A5	1.9	2.0	A13	4.3	2.0
A6	2.0	2.0	A14	4.5	2.0
A7	2.3	2.0	A15	5.0	2.0
A8	2.5	2.0			

Ⓕ	Dust film	1	Polyimide tape		
Ⓔ	Terminal	4	Brass	Silvering	
Ⓗ	Reed	1	SUS	Silver covered	
Ⓒ	Base	1	LCP	Black	
Ⓑ	Cover	1	SUS	Nickel plating	
Ⓐ	Button	1	Brass	Yellow	
NO.	Name	Number	Qty	Materil	Remarks

YUANDI® Yuandi Electronics Co, Ltd

design	date	name	TACT SWITCHS
Review	date		
Approved	date	name	TS-1076S-A□B□

					angle	±2'														
					10~30	±0.30														
					5~10	±0.20														
					~ 5	±0.10														
					modify	Review	Approved	Tolerance not specified	Proportion	1:1	unit	mm	gape number							