



技术参数

Technology Parameters

Frequency Range 频率范围: 0 - 6GHz

Impedance 特性阻抗: 50

Insulation Resistance 绝缘电阻: 500M Min

Dielectric Withstanding Voltage 耐压: 200V AC
1Min

Inner Contact Resistance 接触电阻: 20m Max

Outer Contact Resistance 接触电阻: 10 m Max

Voltage Standing wave Ra HVSWR 电压驻波比:
1.3 Max

Mechanical Durably 机械寿命: 100 Cycles

Relative Humidity 相对湿度: 95 R.H.Max

Operating Temperature 工作温度: -40 85度

		new		2015/5/3	A	瀚源
ECN BO.		DESCRIPTION.		DATE.	REV.	
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	RF0206G120CR	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.25
			MODEL NAME	RF0206G120CR		X.x ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx ±0.15
					ANGULAR ±3'	FILE. NO.