


REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




Ordering Information:
A2508WV-F-XP-H - **

- Part No. 1 2
- Color:

- (blank) - Ivory
- BK - Black
- RD - Red
- BL - Blue
- YL - Yellow
- GN - Green
- OR - Orange
- BR - Brown
- GY - Gray
- PK - Pink
- WH - White
- LY - Lemon yellow
- P - Purple
- LE - Light blue
- FY - Vivid yellow


SPECIFICATIONS:

- Current Rating: 3A AC, DC
- Voltage Rating: 250V AC, DC
- Temperature Range: -40° C ~ +105° C
- Contact Resistance: 10mΩ Max
- Insulation Resistance: 1000MΩ Min
- Withstanding Voltage: 1000V AC/minute
- Pin Material: Brass/Tin over Nickel
- Material: Nylon 66, UL94V-0 (White)
- Soldering Temperature: 260° C ±5° C
- Immersion Period: 3-5 seconds



Ordering Information & Dimensions

Circuits	Dimensions (mm)		Circuits	Dimensions (mm)	
	A	B		A	B
2P	2.50	7.50	9P	20.00	25.00
3P	5.00	10.00	10P	22.50	27.50
4P	7.50	12.50	11P	25.00	30.00
5P	10.00	15.00	12P	27.50	32.50
6P	12.50	17.50	13P	30.00	35.00
7P	15.00	20.00	14P	32.50	37.50
8P	17.50	22.50	15P	35.00	40.00



CNJM Joint More Precision electronics Co.,Ltd.

DRAW NO.	DATE	P/N NO:	DRAW NAME:
DESIGN: 陈雪峰	2018.03.29	A2508WV-F-NP-H	2.50mm pitch 180° wafer
CHECK: 杨焯			
REVIEW:		REV. A/1	SCALE 2.5:1
		UNIT: mm	SHEET: 1 OF 1