



目錄 MAPX	設變內容 MODIFICATION	日期 DATE
------------	----------------------	------------

- 电气特性:Electrical:
1. 额定电流: Current Rating
1.5A/contact terminal
 2. 额定电压: Voltage Rating
30V DC
 3. 接触阻抗: Contact Resistance
30 milliohms MAX
 4. 耐电压: Dielectric Withstanding Voltage:
500 V AC AT Sea Level
 5. 绝缘阻抗: Insulation Resistance:
1000MEGA ohms MIN
- 物理性能: Mechanical:
1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf (MAX)
Unmate force: 1.02kgf (MIN)
 2. 端子保持力: Terminal Retention
1.2kgf (MIN)
 3. 寿命: 1500次
- 原材料: Material:
1. 塑胶: Housing: LCP BK
 2. 端子: Contact: Copper Alloy C2680
 3. 外壳: Shell: C2680
- 电镀: Finish:
1. 端子 Contact: Au 0.7u" Plated on contact area
Tin50u" Plated on solder area
Nickel 50u" Plated underplating over all.
 2. 外壳 Shell: Nickel 50u" Min plating over all.

Pin NUMBER		SIGNAL NAME		产品图 PRODUCT CHART DWG		深圳市精拓金电子有限公司							
1	VBUS			公差一览表 TOLERANCE UNLESS OTHERWISE		单位 UNITS	MM	制图 DRAWING	林属升	产品料号 PRODUCT PART NO.	912-112A2021S10100		
2	D-			.X ±0.25 .X' ±5'		比例 SCALE	1:1	审核 CHKD	郭志富	产品名称 PRODUCT NO.	AF10.6D款前两脚有边方弹 铜壳LCP黑胶6.2SMT		
3	D+			.XX ±0.15 .XX' ±1'							日期 DATE	2015/10/20	核准 APPD
4	GND			.XXX ±0.10 .XXX' ±0.5"									